


SSR10HS-06385

Aliases (UALR10HS063850)

KEMET, SSR10VS/HS, AC Line Filters, Common Mode, 38.5 mH



Click [here](#) for the 3D model.

Dimensions	
L	22mm MAX
T	18mm MAX
H	13.5mm MAX
LL	3.5mm +/-0.5mm
S	17mm +/-0.5mm
S1	12mm +/-0.5mm
Wire Size	0.25mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	300
Typical Component Weight	9 g

General Information	
Series	SSR10VS/HS
Style	Through-Hole
Features	Compact Size, Low Profile, Light Weight, High Frequency, Broad Bandwidth
RoHS	Yes
Miscellaneous	50 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	38.5 mH (10 kHz)
Current	600 mA
Temperature Range	-25/+120°C
DC Resistance	1.2 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.