




Click [here](#) for the 3D model.

Dimensions	
L	23mm MAX
T	23mm MAX
H	14.5mm MAX
LL	3.5mm +/-0.5mm
S	10mm +/-0.5mm
S1	18.5mm +/-0.5mm
Wire Size	0.28mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	420
Typical Component Weight	13 g

General Information	
Series	SSR21NV/NH
Style	Through-Hole
Features	Compact Size, Light Weight, High Performance, Low DCR, High Impedance, Strong Inductance
RoHS	Yes
Miscellaneous	45 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	50 mH (10 kHz)
Current	600 mA
Temperature Range	-40/+120°C
DC Resistance	0.76 Ohms