

INDUSTRIAL patch cables													
i Web code: #2675													
Protocol		PROFINET / EtherCAT® / Sercos®								PROFINET / EtherCAT® / Sercos®			
Transmission		CAT5 (up to 100 Mbps)								CAT5 (up to 100 Mbps)			
Cable		93B / 93C / 93K / 93M / 93R											
Configurable item*		1247656				1247661				1247660	1247629	1247652	1247633
Cable		93B	93C	93M	93K	93B	93C	93M	93K	93B			
Length	0.5 m	1112785	1112939	1112925	1112931	1112877	1112871	1113336		1113311	1113322	1113292	1113297
	1.0 m	1112817	1112937	1112924	1112930	1112876	1112857	1113335		1113304	1113321	1113291	1113295
	2.0 m	1112820	1112936	1112923	1112929	1112875	1112870	1113334		1113310	1113320	1113290	1113294
	3.0 m	1112823	1112935	1112921	1112928	1112874	1112869	1113333	1112858	1113309	1113319	1113289	1113293
	5.0 m	1112856	1112933	1112920	1112927	1112873	1112868	1113332	1113178				

Standard item in fixed length (other lengths available via web code [#2675](#))

* Configurable cable and length between 0.5 m and 90 m

INDUSTRIAL patch cables, angled					
i Web code: #2675					
Protocol	Ethernet				
Transmission	CAT5 (up to 1 Gbps)		CAT6 _A (up to 10 Gbps)		
Cable	94B / 94C / 94D		94F		
Configurable item*	1247639	1247647	1387606	1387607	
Cable	94C	94C	94F	94F	
Length	0.3 m	1112918	1113331	1113823	1113204
	0.5 m	1112916	1113212	1112909	1113202
	1.0 m	1112914	1113211	1112908	1113198
	2.0 m	1112913	1113210	1112907	1113197
	5.0 m	1112912	1113209	1112906	1113196

Standard item in fixed length (other lengths available via web code [#2675](#))

* Configurable cable and length between 0.5 m and 90 m

RJ45

RJ45 patch cables			
Web code: #2676			
Transmission		CAT5 (up to 1 Gbps)	CAT6 _A (up to 10 Gbps)
Sheath material		LSZH	
Cable design		4 x 2 x 26/7 AWG	
Shielding		S/UTP	S/FTP
Length	0.3 m	1227558	1227572
	0.5 m	1227559	1227573
	1.0 m	1227560	1227575
	1.5 m	1227561	1227578
	2.0 m	1227562	1227580
	3.0 m	1227563	1227581
	5.0 m	1227564	1227583
	7.5 m	1227565	1227585
	10.0 m	1227566	1227588
	12.5 m	1227567	1227590
	15.0 m	1227570	1227591
	20.0 m	1227571	1227593
	25.0 m		1367335
	30.0 m		1367336
	50.0 m		1367337

RJ45 patch cables, unshielded					
i Web code: #1712					
Transmission		CAT5 (up to 1 Gbps)			
Sheath material		PVC			
Cable design		4 x 2 x 24/7 AWG			
Shielding		UTP			
Length	0.5 m	1413086	Length	5.0 m	1410694
	1.0 m	1410595		10.0 m	1412973
	2.0 m	1410596		15.0 m	1412971
	3.0 m	1413019		20.0 m	1412974

For more color versions, visit our web shop.