

Illuminated pushbutton Ø 22 mm silver contact

82-6552.2134



<https://eao.com/p/82-6552.2134>

Your product:



82-6552.2134

Illuminated pushbutton Ø
22 mm silver contact

FRONT

Front bezel shape:	flush
Front bezel material:	Aluminium

MOUNTING

Mounting cut-out:	Ø 22 mm
-------------------	---------

OPERATING-/INDICATION PART

Illumination colour:	Green
Shape of illumination:	Ring
Lens optics:	opaque
Lens illumination:	illuminative
Lens material:	Aluminium
Lens colour:	Nature
Lens shape:	flush

ELECTRICAL CHARACTERISTICS

Electrical lifetime:	50 000 cycles of operation
Switching voltage and switching current:	

according to IEC 60947-5-1 (Silver contacts)	
Service categorie AC-15	
Voltage	Current
24 VAC	1 A
35 VAC	1 A (M12 version)
110 VAC	1 A
220 VAC	0.5 A
Switch rating DC service categorie DC-13 (Silver contacts)	
Voltage	Current
24 VDC	0.7 A
35 VDC	0.5 A (M12 version)
110 VDC	0.2 A
220 VDC	0.1 A

according to UL 508 (Silver contacts)	
cosφ 0,75 ... 0,8	
Voltage	Current
120 VAC	5 A
240 VAC	3 A
24 VAC	1 A

Thermal current Ith:	5 A
Rated insulation voltage Ui:	250 V
Pollution degree:	2, according to EN IEC 60947-1
Electric strength:	1500 VAC, 50 Hz 1 minute between life terminals and ground
Contacts:	1 C
Rated Operational Voltage Ue:	250 VAC
Operating voltage:	24 V AC/DC

MECHANICAL CHARATERISTIC

Switching action:	Maintained
Contact material:	Silver
Operating Travel:	ca. 3 mm
Weight:	0.018 kg
Tightening torque:	0.5 ... 0.6 Nm, Screw terminal 0.1 Nm
Operating force:	4 N ... 7 N
Terminal:	Screw terminal
Switching system:	Snap-action switching element
Mechanical lifetime:	500 000 cycles of operation

AMBIENT CONDITION

Vibration resistance:	10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6
Storage temperature:	

– 40 °C ... + 80 °C

Operating temperature:

– 30 °C ... + 70 °C

Climate resistance:

Damp heat, 21 days according to IEC 60512-11

Shock resistance:

Max. 500 m / s² as per IEC 60068-2-27

CERTIFICATE

Conformities:

CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

Approbations:

CB, CCC, C UL, UL

OTHER


Kind of illumination:

Single-LED

Short Description:


Illuminated pushbutton Ø 22 mm silver contact, Maintained, 24 V AC/DC, 1 C, Screw terminal, Aluminium, Green, Nature

Dimension drawings:




A = Solder terminal
B = Screw terminal

Component layouts:



Mounting cut-outs:



Wiring diagrams:

