

Actuator

46-
2231.11J0.000



<https://testing.eao.com/p/46-2231.11J0.000>

Your product:



46-2231.11J0.000

Actuator

FRONT

Front bezel colour:	Black
Front form:	round
Front bezel material:	Plastic
Front dimension:	Ø 29 mm

MOUNTING

Mounting cut-out:	Ø 22.3 mm
Design:	raised

OPERATING-/INDICATION PART

Lens colour:	Blue
Lens material:	Plastic
Lens illumination:	illuminative
Lens shape:	flush
Lens optics:	transparent

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Mechanical lifetime:	1 Mio. cycles of operation

Weight: 0.019 kg

Switching action: Momentary

AMBIENT CONDITION

Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

IP front protection: IP65

IK front protection: IK03

Shock resistance: 30g, 18ms (EN-IEC 60068-2-27)
50g, 11ms (EN-IEC 60068-2-27)

Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

Operating temperature: - 25 °C ... + 55 °C

CERTIFICATE

Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

Approbations: CSA, EAC, UL

Conformities: CE

OTHER


Short Description: Actuator, Ø 22.3 mm, Ø 29 mm, flush, illuminative, Blue, Plastic, transparent, round, Black, Plastic, Momentary, IP65, IK03

max. number of switching elements: 8

Housing colour: Black

Housing material: Plastic

Dimension drawings:



Mounting cut-outs:

