

Actuator

46-
2234.31H0.000



<https://testing.eao.com/p/46-2234.31H0.000>

Your product:



46-2234.31H0.000 Actuator

FRONT

Front form:	round
Front dimension:	Ø 29,5 mm
Front bezel material:	Metal
Front bezel colour:	Silver

MOUNTING

Mounting cut-out:	Ø 22.3 mm
Design:	raised

OPERATING-/INDICATION PART

Lens illumination:	illuminative
Lens colour:	Green
Lens optics:	transparent
Lens shape:	flush
Lens material:	Plastic

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Switching action:	Maintained
Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)

Weight: 0.033 kg

Mechanical lifetime: 500 000 cycles of operation

AMBIENT CONDITION

Shock resistance: 50g, 11ms (EN-IEC 60068-2-27)

IK front protection: IK03

Operating temperature: – 25 °C ... + 55 °C

Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

IP front protection: IP65

Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

CERTIFICATE

Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

Conformities: CE

OTHER

Housing material: Plastic

Short Description: Actuator, Ø 22.3 mm, Ø 29,5 mm, flush, illuminative, Green, Plastic, transparent, round, Silver, Metal, Maintained, IP65, IK03

max. number of switching elements: 6

Housing colour: Black

Dimension drawings:

