

Actuator

46-

2531.1920.000



<https://testing.eao.com/p/46-2531.1920.000>

Your product:



46-2531.1920.000 Actuator

FRONT

Front bezel colour:	Yellow
Front bezel material:	Plastic
Front form:	round
Front dimension:	Ø 40 mm

MOUNTING

Design:	raised
Mounting cut-out:	Ø 22.3 mm

OPERATING-/INDICATION PART

Lens optics:	opaque
Lens shape:	mushroom-head
Lens illumination:	non illuminative
Lens colour:	Red
Lens material:	Plastic

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Weight:	0.036 kg
Mechanical lifetime:	1 Mio. cycles of operation

Switching action: Momentary

Tightening torque: 2 ... 3 Nm (17.7 ... 26.6 Lb-in)

AMBIENT CONDITION

Shock resistance: 30g, 18ms (EN-IEC 60068-2-27)
50g, 11ms (EN-IEC 60068-2-27)

Operating temperature: – 25 °C ... + 55 °C

Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

IP front protection: IP65

Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

IK front protection: IK03

CERTIFICATE

Approbations: CSA, EAC, UL

Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

Conformities: CE

OTHER


Short Description: Actuator, Ø 22.3 mm, Ø 40 mm, mushroom-head, non illuminative, Red, Plastic, opaque, round, Yellow, Plastic, Momentary, IP65, IK03

max. number of switching elements: 6

Housing colour: Yellow

Housing material: Plastic

Mounting cut-outs:



Dimension drawings:

