

Product Information

35 52 145 ESD

Electronics Pliers ESD

With box joint



- Robust, load-optimized construction with through-pinned and backlash-free precision joint
- Head carefully rounded: no sharp edges that could damage the material
- Electrically discharging handles - dissipative
- High, slim sleeves for fine and comfortable gripping between thumb and index finger
- Uniform bending behavior for a more direct sense of work
- Smoothly ground gripping surfaces for damage-free gripping
- Low-friction double spring for smooth and even opening
- The mirror polish in combination with a fine oil film provides rust protection - no circuit faults caused by peeling chrome from plated tools
- Flat, wide jaws, smoothly ground gripping surfaces

General	
Article No.	35 52 145 ESD
EAN	4003773089223
pliers	mirror polished
head	mirror polished
handles	with multicomponent handles
Weight	86 g
Dimensions	145 x 66 x 17 mm
Standard	DIN ISO 9655 DIN EN 61 340-5
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Jaw length (B)	34.1 mm
Jaw thickness (joint) (D)	8.5 mm
Tips width (E)	2.5 mm
Tips thickness (F)	1.8 mm
Head width (A)	13.0 mm
ESD	yes

Technical changes and errors excepted



