

Product Information

95 12 225

KNIPEX StepCut® XL

Cable shears with step cut



- High-leverage joint, long handles and optimised cutting edges: noticeably easier cutting than with compact cable shears
- Large cutting capacity: cuts solid copper or aluminium cables up to 35 mm², stranded cables up to 70 mm² and fine stranded cables up to 120 mm²
- Dual cutting areas: Stepped cutting edge holds small and larger cables close to the joint during the cut; the front cutting edge cuts very large cables step by step
- Easy one- or two-handed operation with minimum handle opening for large cable diameters
- Adjustable, high-leverage bolted joint provides precise and smooth cutting
- Slim head for easier accessibility
- Pinch guard prevents operators' fingers being pinched
- Not suitable for steel-reinforced cables, e.g. ACSR
- Cutting edges additionally laser-hardened, cutting edge hardness approx. 56 HRC
- With comfort handles: consisting of three ergonomic components for optimized handling and equipped with two KNIPEXtend interfaces for extensions

General	
Article No.	95 12 225
EAN	4003773088899
Shears	burnished
head	burnished
handles	with comfort handles
Weight	425 g
Dimensions	232 x 60 x 25 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical changes and errors excepted

