

Product Information

77 02 130 ESD

Electronics Diagonal Cutters ESD

With box joint

- Durable, load-optimised design with backlash-free box joint
- High, slim sleeves for fine and comfortable gripping between thumb and index finger
- Electrically discharging handles - dissipative
- Less physical effort due to very high transmission ratio
- Load-optimised for a more direct feel when working
- Low-friction double spring for smooth and even opening
- The mirror polish in combination with a fine oil film provides rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 62 HRC
- Round head, with small bevel



General	
Article No.	77 02 130 ESD
EAN	4003773089209
head	mirror polished
handles	with multicomponent handles
Weight	81 g
Dimensions	130 x 50 x 18 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacities medium hard wire (diameter)	Ø 1.5 mm
Cutting capacities hard wire (diameter)	Ø 0.8 mm
Jaw length (B)	16.2 mm
Jaw thickness (joint) (D)	8.5 mm
Head width (A)	13 mm
Cutting edge length mm (C)	16.2 mm
ESD	yes

Technical changes and errors excepted

