


Ball End Screwdrivers

- ProGuard™ Finish -

- Ball End inserts into screw at a 25° angle
- Ergonomic handle design
- Non-slip grip
- Two component handle with tough inner core and cushioned rubber exterior
- Anti-roll design



ProGuard™ finish delivers superior corrosion protection



Ball End Tips

Screwdrivers

Handles are color coded for easy recognition

Yellow=Inch

Red=Metric

Sets	PART#	MODEL#	PCS	LENGTH	CONTENTS	QTY	LIST
Inch	10645	BSX7	7	Standard	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"	1	
	10632	BSX8S	8	Standard	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"	1	
	10633	BSX8	8	Standard	7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16"	1	
	10637	BSX13	13	Standard	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	1	
	10737	BSX11L	11	Long	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	1	
Metric	10686	BSX6M	6	Standard	1.5, 2, 2.5, 3, 4, 5mm	1	
	10687	BSX7M	7	Standard	1.27, 1.5, 2, 2.5, 3, 4, 5mm	1	
	10699	BSX9M	9	Standard	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10mm	1	
	10733	BSX8ML	8	Long	2, 2.5, 3, 4, 5, 6, 8, 10mm	1	



10637

    PACKAGED  SINGLE PACKAGING  TAGGED/BARCODED     PACKAGED  SINGLE PACKAGING																								
Singles	SIZE	INCH	MM	INCH	MM	PART#	QTY	LIST	EA	PART#	QTY	LIST	EA	SIZE	INCH	MM	INCH	MM	PART#	QTY	LIST	EA		
Inch	Standard									Long														
	.050	2.4	60	4.1	104	10602	2			40602	2			-	-	-	-	-	-	-	-	-	-	
	1/16	2.5	64	4.7	118	10603	2			40603	2			-	-	-	-	-	-	-	-	-	-	
	5/64	2.6	67	4.8	122	10604	2			40604	2			5/64	4.3	110	6.5	164	10704	2				
	3/32	2.8	71	5.2	132	10605	2			40605	2			3/32	4.8	122	7.2	184	10705	2				
	7/64	2.9	74	5.3	136	10606	2			40606	2			7/64	5.9	151	8.4	212	10706	2				
	1/8	3.1	80	6.6	168	10607	2			40607	2			1/8	6.4	164	9.9	252	10707	2				
	9/64	3.3	83	6.8	171	10608	2			40608	2			9/64	6.9	176	10.4	264	10708	2				
	5/32	3.6	91	7.9	201	10609	2			40609	2			5/32	7.4	189	11.8	299	10709	2				
	3/16	3.7	94	8.0	204	10610	2			40610	2			3/16	7.9	202	12.3	312	10710	2				
	7/32	4.2	107	9.0	230	10611	2			40611	2			7/32	8.4	214	13.3	337	10711	2				
	1/4	5.0	126	9.8	249	10612	2			40612	2			1/4	8.9	227	13.7	349	10712	2				
	5/16	5.6	142	10.4	265	10613	2			40613	2			5/16	9.5	241	14.3	364	10713	2				
	3/8	6.5	164	11.3	287	10614	2			40614	2			3/8	9.9	252	14.8	376	10714	2				
	7/16	7.6	194	12.5	317	10615	1			-	-			-	-	-	-	-	-	-	-	-	-	
	1/2	8.6	217	13.4	340	10616	1			-	-			-	-	-	-	-	-	-	-	-	-	
Metric	Standard									Long														
	1.27	2.4	60	4.1	104	10649	2			40649	2			-	-	-	-	-	-	-	-	-	-	
	1.5	2.6	66	4.7	120	10650	2			40650	2			-	-	-	-	-	-	-	-	-	-	
	2.0	2.8	72	5.0	127	10652	2			40652	2			2.0	4.0	102	6.2	157	10752	2				
	2.5	2.7	69	5.1	130	10654	2			40654	2			2.5	4.3	110	6.7	171	10754	2				
	3.0	3.3	83	6.7	171	10656	2			40656	2			3.0	6.2	158	9.7	247	10756	2				
	3.5	3.5	88	6.9	176	10658	1			40658	1			-	-	-	-	-	-	-	-	-	-	
	4.0	3.7	95	8.1	205	10660	2			40660	2			4.0	7.0	179	11.4	288	10760	2				
	4.5	4.3	109	8.6	218	10662	1			-	-			-	-	-	-	-	-	-	-	-	-	
	5.0	4.3	109	8.6	219	10664	2			40664	2			5.0	7.8	198	12.1	308	10764	2				
	5.5	5.0	126	9.3	236	10666	1			-	-			-	-	-	-	-	-	-	-	-	-	
	6	5.4	137	10.2	260	10668	2			40668	2			6	8.6	218	13.4	341	10768	2				
	7	5.7	145	10.5	268	10670	1			-	-			-	-	-	-	-	-	-	-	-	-	
	8	6.4	162	11.2	286	10672	2			40672	2			8	9.3	237	14.2	360	10772	2				
	9	6.9	175	11.7	298	10674	1			-	-			-	-	-	-	-	-	-	-	-	-	
	10	7.3	184	12.1	307	10676	2			40676	2			10	10.2	259	15.0	382	10776	2				

For Extra Long Length Singles see page 44