

Active Optical (AOC) 8K DisplayPort cable "AOC Premium Series", 30 m

CC-DP8K-AOC-30M



- Active Optical Cables (AOC) use fiber optic technology to transport the digital video signal. This means that the signal can be carried much further than with a traditional copper cable (up to 100 m), and reduces the risk of EMI/RFI interference. DisplayPort AOC cables also have dedicated copper power wires inside, so no external power supply is required.
- DisplayPort AOC cable uses fiber optic technology reduces the risk of EMI/RFI in high interference environments
- Durable extra thin premium quality cable with stylish metal connectors
- Smaller cable diameter compared to traditional copper DP cables
- Supports 8K UHD resolutions at 60Hz

Features

- Premium DisplayPort AOC cable
- Supports video resolutions up to 8K at 60 Hz
- Fiber optic cable is highly resistant to EMI and RFI interference
- Premium metal connectors
- Gold plated connectors for perfect image quality
- Compatible with all devices that support DisplayPort

Packaging

Q'ty in crtn, pcs	10
Crtn volume, CUM	0.037
Crtn weight, kgs	9.71
Individual package size LxWxH:	222x69x210 mm
Carton size LxWxH:	445x230x360 mm
Country of origin	CN
Barcode	8716309129176
Customs code	8544429090

Specifications

Interface: DisplayPort v.1.4
 Connectors: 2x Displayport (male)
 Supported resolution: 8K @ 60 Hz or 4K @ 120 Hz
 Conductor material: fiber optic
 Diameter: 4.5 mm
 Cable length: 30 m

Certificates

