

UTP Cat6 Patch cord, grey, 15 m, copper

PP6U-CU-15M

- Perfect connection
- Gold plated contacts



Specifications

Category: category 6
 Type: UTP (unshielded)
 Frequency bandwidth: Max. 250 MHz
 Compliance with ANSI / TIA / EIA-568B standards
 Conductor: AWG 26 4P(7 x 0.16 mm wire), pure copper
 Conductor insulation: HDPE 0.85 mm
 Shielding: n/a
 LDPE filler: yes
 Polyester tape: n/a
 Drain wire: n/a
 Jacket material: PVC
 Jacket braiding: n/a
 Jacket outer diameter: 6.2 mm
 Length: conform item description
 Color: conform item description

Features

- Copper CAT6 stranded unshielded (UTP) patch cord, 8P8C
- Snagless boots

Packaging

Q'ty in crtn, pcs	20
Crtn volume, CUM	0.048
Crtn weight, kgs	9.18
Individual package size LxWxH:	250x175x50 mm
Carton size LxWxH:	400x300x400 mm
Country of origin	CN
Barcode	8716309131360
Customs code	8544421000

Certificates

