

USB 2.5G Gigabit network adapter, space grey

A-USB3AC-LAN2G-01

- Plug-&-Play
- 2.5 x faster as Gigabit networking
- Perfect for online gaming, UHD movies and (remote) office work



Features

- USB 3.1 2.5G Gigabit network adapter
- Practical USB Type-A + Type-C combo-connector
- Supports 10/100/1000/2500 Mbps Gigabit LAN network
- Durable premium style metal housing
- Plug & Play

Packaging

Q'ty in crtn, pcs	96
Crtn volume, CUM	0.04752
Crtn weight, kgs	6.88
Individual package size LxWxH:	
Carton size LxWxH:	480x330x300 mm
Country of origin	CN
Barcode	8716309130424
Customs code	8522900090

Package contents

Adapter
User manual

Specifications

Interface: USB 3.1 gen. 1
 Connector 1: USB Type-A male
 Connector 2: USB Type-C male
 Connector 3: LAN RJ-45 female
 LAN: 2.5 Gigabit (IEEE 802.3 10Base-T, IEEE 802.3u 100Base-TX, IEEE 802.3ab 1000Base-T, IEEE 802.3bz 2.5GBase-T)
 Data transfer rate: Max. 2500 Mbps
 Power consumption: 5 VDC up to 1 A
 Cable length: 15 cm
 Dimensions: 63 x 23 x 14 mm
 Net weight: 36 g
 Chipset: RTL8156B

System requirements

Windows 7/8/10/11
 MacOS 10.7 to 10.15, 11.0, 12.0, 13.0
 Free USB 3.x (2.0) port

Certificates

