

POSAC-C13-5/UK18 series

AC Power Cable



model

POSAC-C13-5/UK18

AC Power Cable with BS1363 plug & C13 plug, 1.8m long

mechanical specification

connector type (output)	IEC-C13
connector type (input)	BS1363
length	1800mm
core area	3x0.75mm ²
wire construction	pure copper core, flexible, multiwire conductors
insulation material	PVC
inner conductor	Cu
external dimensions of the cable	5.8 mm
color of the cores	black

electrical specification

nominal voltage	0 - 300VAC
rated current	5A
Insulation resistance	>100MΩ @ 500VAC
Insulation thickness	0.5mm / 0.6mm
Wire resistance	max 0.044Ω/m
Working Temperature	-40°C ÷ 70°C

safety

RoHS	RoHS 2015/863
LVD	LVD 2014/35/UE

POSAC-C13-5/UK18 series

AC Power Cable



mechanical specification

