

Molecular Sieve

20-055-00xx

Product specifications

Material: Molecular Sieve
 Bag: Non-woven
 Weld width: ≥ 4 mm
 Complies with: US FDA 21 CFR 177.1520
 Storage: Store in a dry place
 between 10 and 40°C
 Shape : Balls



Part Number and Features

Part Number	Unit	Quantity per box	Moisture	% Absorbed moisture	Bag (+/- 5mm)
20-055-0010	10g	800	5% 10%	13% 15%	70mm x 60mm Tyvek
20-055-0015	15g	500	5% 10%	13% 15%	75mm x 90mm Non-woven
20-055-0025	25g	300	5% 10%	13% 15%	100mm x 54mm Non-woven
20-055-0030	30g	500	5% 10%	13% 15%	110mm x 54mm Tyvek
20-055-0045	45g	300	5% 10%	13% 15%	115mm x 100mm Tyvek

Options

Other dimensions on request
 Clay desiccants available