

ESD REEL BOXES

23-173/172-xxxx

Product specifications

Material:	Conductive carbon-loaded PE
Color:	Black
Surface resistance:	$<10^5 \Omega$
Thickness:	1.8mm
Shelf life:	Permanent
Heavy metals:	< 100 ppm

Material properties

Using temperature (max):	60°C
Elasticity:	1200 Mpa
Impact resistance:	11kJ/m ²
Tensile strength at break:	33 Mpa



Part Numbers and dimensions

Reference	External dimensions (LxWxH) mm	Compartment Width (mm)	Compartments
23-173-1732	300 x 200 x 180	20	15
23-173-1384	500 x 200 x 180	20	25
23-172-2125	500 x 350 x 200	20	25
23-172-1683	500 x 350 x 320	30	16

Other dimensions available, upon request