

Power USB-C Double Socket PD/QC with Mounting Plate
without LED

Art. No. 67372050 (BP)

Art. No. 67372550 (SP)

08.08.2024

Input voltage: 8 - 30 V DC

Output USB-C1:

Input Voltage	Output voltage	Output current max.
12,0V	5,0V	3,0A
	9,0V	3,0A
	12,0V	2,5A
24,0V	5,0V	3,0A
	9,0V	3,0A
	12,0V	2,5A
	15,0V	2,0A
	20,0V	1,5A

Output USB-C2:

Input Voltage	Output voltage	Output current max.
12,0V	5,0V	3,0A
	9,0V	3,0A
	12,0V	2,5A
24,0V	5,0V	3,0A
	9,0V	3,0A
	12,0V	2,5A
	15,0V	2,0A
	20,0V	1,5A

Power USB-C Double Socket PD/QC with Mounting Plate without LED

Art. No. 67372050 (BP)

Art. No. 67372550 (SP)

08.08.2024

USB-C1 and USB-C2 outputs are independent of each other, they can be used individually or together.

Output power according to PD and QC protocol:

USB-C 1,2 (PD): 30 W each

Output power max.: 2 x 30 W

Charging protocol C-socket: Power Delivery (PD), Quick Charge, PPS

Current consumption: max. 5 mA (idle)

Protection against: short circuit, overload, overvoltage,
reverse polarity and overtemperature

Panel thickness: no matter

Installation hole: 28 mm Ø for panel thickness up to 14 mm
36 mm Ø for panel thickness over 14 mm

Material:

Housing: Makrolon

Mounting plate: ABS

Temperature load: max. 110 °C

Cable:

Stranded cable: 2 x 0,5 mm² red (+) / black (-)

Length: 150 mm

Power USB-C Double Socket PD/QC with Mounting Plate
without LED

Art. No. 67372050 (BP)

Art. No. 67372550 (SP)

08.08.2024

