




DRAWING

- 1.CABLE:NO UL 14C+1.<(28AWG,7/0.12mm±0.008)×14C
SHIELD:DRAIN WIRE+AL/MY COVERAGE
JACKET:PVC,COMPLIANCE ROHS,COLOR:BEIGE,Ø.D:6mm±0.2mm
- 2.CONNECTOR:2 PCS HDD15 PIN MALE SOLDER TYPE CONNECTOR
SHELL:NICKEL PLATED
- 3.CONNECTOR:2 PCS HDD15 PIN FEMALE SOLDER TYPE CONNECTOR
SHELL:NICKEL PLATED
- 4.HOOD:PVC MOLDED TYPE WITH AL-FOIL SHIELDED ON INNER
MOLD INJECTION OUTER MOLD WITH THUMB SCREW#4-40UNC
HOOD COLOR IS BEIGE,COMPLIANCE ROHS
- 5.Fulfill ROHS Guideline
- 6.ELECTRONIC TEST: 100% OPEN SHORT+MISS WIRE TEST

HDD15PIN PLUG(P1)	WIRE	HDD15PIN JACK(P2)
1	---	1
2	---	2
3	---	3
4	---	4
5	---	5
6	---	6
7	---	7
8	---	8
10	---	10
11	---	11
12	---	12
13	---	13
14	---	14
15	---	15
SHELL	D.W	SHELL

PART NO	C-15GW/1,8	SHEET NO	1	 THIRD ANGLE PROJECTION	有得 限公 股 份 NEWMAN, HOPE & CO. INC		
TITLE: HDD15 PIN PLUG TO HDD15 PIN JACK BEIGE COLOR,L:1.8M				SCALE		N.T.S	DRAWN BY & DATE
				SIZE		A4	CHECKED BY & DATE
				UNIT		APPROVED BY & DATE	
DWN NO	D-C-15GW/1,8			☒ mm ☐ INCH	TEL:886-2-28765517 FAX:886-2-28765527 E-MAIL: sales@newmanhope.com.tw		