


ROCKER SWITCH MODEL MR SERIES





RATING:12(4)A 125/250V~ (cURus/ENEC15)

10(4)A 250V~T125/55(CQC)

DIELECTRIC WITHSTAND VOLTAGE:1500VAC FOR 1 MINUTE

INSULATION RESISTANCE:DC 500V 100MΩ (MIN)

CONTACT RESISTANCE: 20mΩ INITIAL (MAX)



PANEL THICKNESS:1.0~2.0mm

NOTE:TOLERANCES UNLESS OTHERWISE SPECIFIED:± .012/0.3 (in/mm)

REVISION	DESCRIPTION	REVISED BY	TOLERANCES			ANGLE $\frac{1}{2}^{\circ}$		UNIT	mm	PART NAME	MR SPEC DRAWING	DWG NO
			DRAWN BY	奚康平	DESIGNED BY	邹红海	SCALE	2/1				PART NO
			CHECKED BY		APPROVED BY		DATE	2023.12.18				
 2023.12.18	首次出圖	奚康平										