

Plugs

SLS 20 B



Product	SLS 20 B
description	Touch protected plug to assemble with screw connection for cables up to 1.5mm². Insulated by latching and sprung insulating sleeve, to be released by pressure on the lateral locking spring. plug with contact spring, 4mm diameter. *Apply to this typ 150 VDC, CAT II; according IEC / EN 61010-031 item 6.4.2; allowed for devices that are equipped with terminals which cannot accept fully shrouded connectors.
operating instruction	BA413
article-no. / *colour	9318251xx ● 00 black ● 01 red ● 02 blue ● 03 yellow ● 04 green ● 07 white Ni
drawing	
technical data	
connection	screw terminal
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
rated current (consider derating curve)	16 A
material plug	brass, nickel plated
housing material	POM
temperature range acc. To IEC61010 ⁽¹⁾	-25 °C to +80 °C

4 mm sliding sleeve system

inflammability class acc. to UL 94 (only valid for basic material of housing)	HB
--	----

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges

⁽²⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 21.06.2022

stand: 21.06.2022