


Crocodile clips

AK 2 B



Product	AK 2 B
description	Contact-protected, high strength alligator clip. Clamping range up to a bolt diameter of 9.5 mm. The part of the jaws (fine wire section) allows a secure contact to be made when clamping even the thinner wire. 4 mm diameter brass socket connection.
operating instruction	BA465
article-no. / *colour	9324351xx  00 black  01 red Ni
drawing	
	
technical data	
connection	unsprung socket 4 mm
rated voltage	AC/DC 300 V
measurement cat. acc. to IEC 61010	CAT II
rated current (consider derating curve)	25 A
material socket	brass, nickel plated
housing material	PP
temperature range acc. To IEC61010 ⁽¹⁾	-25 °C to +80 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB
clamping range	9,5 mm

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges
stand: 21.06.2022

stand: 21.06.2022