

Set

PMS SKS Elektronik



Product	PMS SKS Elektronik
description	Service Case electronic for all tasks of development, service, education and more. - PRUEF 2610 FT - safety-test probe, shatter-proof insulated sleeve with slender, spring-loaded stainless steel tip - MICRO-PRUEF MPS 2 0.64 FT - miniature test probe with slender, spring-loaded stainless steel tip, for sampling of SMD components - MICRO-KLEPS - miniature test clips with 0,64mm connecting plugs and rotating gripper (SMD technology) - KLEPS 064 PCH - miniature test clips with 0,64mm plug for tapping from pins and wires up to Ø 1mm - MZS 4 - overmolded plug adapter from 4mm plug to 2mm socket - MICRO-SMD CLIP 1 - two-pole test clip for SMD components with flat gripper, electrically insulated spring and 0,64mm sockets - MA 260 SH - safety miniature alligator clip with 4mm connecting socket, clamping distance: fine wires up to Ø 6mm - AK 2 B 2540 I - wide-opening, contact protected alligator clip, for bolt diameter up to 30mm - MLS WS 50/2.5 - safety-test lead, both sides with Ø 4mm stackable safety plugs (length: 50 cm) - MAL N 4-0.64/100-0.25 - overmolded test lead with 4mm spring-loaded plug with onward connection capability and 0,64mm insulated connecting socket (length: 100 cm) - MKL 0.64/25-0.25 - test lead, on both sides 0,64mm insulated connecting sockets (length: 25 cm) - BNC AL 0.64 - BNC adapter cable with two insulated 0.64 mm connecting sockets for measuring - 2-footer-positioner
Articlenummer	932791001
technical data	
scope of delivery	1x test probe PRUEF 2610 FT black (972 318-100) 1x test probe PRUEF 2610 FT red (972 318-101) 1x test probe MICRO-PRUEF MPS2 0,64FT black (973 995-100) 1x test probe MICRO-PRUEF MPS2 0,64FT red (973 995-101) 1x clamp-type test probe MICRO-KLEPS black (973 972-100) 1x clamp-type test probe MICRO-KLEPS red (973 972-101) 1x clamp-type test probe KLEPS 064 PCH black (974 201-100) 1x KLEPS 064 PCH red (974 201-101) 1x KLEPS 064 PCH blue (974 201-102) 1x KLEPS 064 PCH yellow (974 201-103) 1x KLEPS 064 PCH green (974 201-104) 1x KLEPS 064 PCH grey (974 201-106) 1x KLEPS 064 PCH white (974 201-107) 1x plug MZS 4 black (973 599-100)

System independent

	1x plug MZS 4 red (973 599-101) 1x MICRO-SMD CLIP 1 (972 416-100) 1x crocodile clip MA 260 SH black (973 889-100) 1x crocodile clip MA 260 SH red (973 889-101) 1x crocodile clip AK 2B 2540I yellow/green (972 405-188) 1x test lead MLS WS 50/2,5 black (934 087-100) 1x test lead MLS WS 50/2,5 red (934 087-101) 1x test lead MLS WS 50/2,5 yellow/green (934 087-188) 1x test lead MAL N4-0,64/100-0,25 black (934 160-100) 1x test lead MAL N 4-0,64/100-0,25 red (934 160-101) 1x test lead MKL 0,64/25-0,25 black (973 604-100) 1x test lead MKL 0,64/25-0,25 red (973 604-101) 1x test lead BNC AL 0,64 black (933 844-001) 1x 2-footer-positioner (974 401-000)
--	---

stand: 10.05.2022

stand: 10.05.2022