


Plugs

MZS 4



Product	MZS 4
description	Injection-moulded adapter plug from 4 mm diameter plug to 2 mm diameter socket. This adapter plug enables the use of unsprung plugs from 2 mm system and sockets from 4 mm system.
operating instruction	BA416
article-no. / *colour	 00 black  01 red Ni
drawing	
	
technical data	
connection	spring loaded socket 2 mm
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
rated current (consider derating curve)	6 A
material plug	brass, nickel plated
housing material	PP
temperature range acc. To IEC61010 ⁽¹⁾	-20 °C to +60 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges

⁽²⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 21.06.2022

stand: 21.06.2022