

Clamp-type test probe

KLEPS 064 PCH



Product	KLEPS 064 PCH
description	The small weight and the compact design offer the possibility to use it at very small components. Can be plugged with MKL(...) and MAL(...) measuring leads
operating instruction	BA002
article-no. / *colour	9742011xx ● 00 black ● 01 red ● 02 blue ● 03 yellow ● 04 green ● 06 gray ● 07 white Au
drawing	
technical data	
connection	unsprung pin Ø 0.64 mm
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
material socket	contact hook: copper beryllium pin: phosphor - bronze
clamp type	contact hook, gold plated
clamping range	1 mm

⁽²⁾ without rated measurement category, for other circuits that are not directly connected to mains
stand: 09.06.2022

stand: 09.06.2022

0.64 mm system