



Qoltec Network SWITCH | 5 x RJ45 port | 100Mbps | Fast Ethernet | LAN

Product code: 52245

The SWITCH network switch is a powerful network device that provides stable and fast connections. It has 5 RJ45 ports for connecting devices on the local network. The maximum signal transmission distance is 150 metres, making it suitable for extensive network installations.

DISCOVER THE FULL POTENTIAL OF YOUR NETWORK



Stable and fast local network

If you are looking for a reliable and efficient network device that provides you with a stable and fast connection and smooth data transmission, then our switch from Qoltec is the ideal choice. Thanks to its innovative technology and robust design, **our device guarantees stable and smooth signal transmission from a single source to up to four devices simultaneously**. This functionality allows for an exceptional expansion of the possibilities of use and exploitation of the multimedia system, **without the need for additional complex solutions or costly investments** in additional equipment. Now you can enjoy your favourite films, video games or presentations on several receivers simultaneously.

FUNCTIONALITY ALWAYS AT HAND




Range up to 150m, full duplex, 5 RJ45 ports with automatic crossover and interference protection

Discover new possibilities with the Qoltec device that offers:

- Signal distance up to 150m,
- **Equipped with 5 RJ45 ports**, each port has an automatic line crossover function,
- 10Mbps at 14880 packets per second, 100Mbps at 14800 packets per second,
- Enables efficient data exchange in full duplex mode compliant with IEEE802.3X, half duplex data flow control,
- Supports up to 1024 MAC addresses,
- **The unit is also distinguished by 8-pin shielded ports** to protect against electromagnetic interference, and an efficient heat dissipation system to ensure reliable operation even under intensive loads,
- **Has LEDs**, which provide information on the current operation of the device,

EXPAND YOUR MULTIMEDIA CAPABILITIES



Simple and quick installation

Our device **offers instant and trouble-free installation**, thanks to Plug & Play technology, which requires no additional configuration or technical expertise. You only need to follow a few simple steps. Firstly, **connect the devices to the appropriate RJ45 ports using the appropriate network cables** and then connect one of the ports to your router or access modem. Make sure the LEDs on the switch indicate activity on the ports.

TRUST CONFIRMED BY WARRANTY

Product with 24 months guarantee

Do you care about the high quality of the product you buy? Our solutions will meet your expectations. **The product is covered by a 24-month warranty** valid from the day of purchase.

TECHNICAL DATA

Producer	Qoltec
Max. bandwidth	1.2Gbps
Max. baud rate	100Mbps
Interface	RJ45
Power supply	5-12V / 0.6A
Usage	Communication, Internet, Router, Server
Additional information	Cable length : 0.65m
Colour	White
Working temperature	-10 C ~ 55
Dimensions (D/L x W x H)	55 x 85 x 20 mm
Package	Box
Package contents	1 x SWITCH 1 x Power Adapter 1 x User manual
Package depth / length [mm]	65
Package width [mm]	90
Package height [mm]	65
Net weight [kg]	0.113
Gross weight [kg]	0.128
Warranty	24 months
EAN code	5901878522456