




Fibre optic diffuse reflection sensor

FT-00-M-V-E3/1,5M



Application		
Function principle	Diffuse reflection sensor	
Application	High temperature resistance; Robust design for use in harsh industrial environments; Resistant to various aggressive chemicals	
Detection zone		
Range with fibre optic amplifier type	OCF; OKF; OOF; OUF	
OCF (High Power)		
Range fibre optics	[mm]	350
OKF		
Range fibre optics	[mm]	36
OOF		
Range fibre optics	[mm]	180
OUF		
Range fibre optics	[mm]	36
Operating conditions		
Ambient temperature	[°C]	-20...150
Mechanical data		
Weight	[g]	108.5
Version of sensing head	straight	
Sensing head diameter	[mm]	3

E20526



Fibre optic diffuse reflection sensor

FT-00-M-V-E3/1,5M

Sensing head length	[mm]	10
Total length	[mm]	1500
Min. bending radius	[mm]	20
Fibre arrangement		⓪
Fibre material		glass
Fibre head material		stainless steel (303/1.4305)
Fibre sheath material		metal silicone
Accessories		
Items supplied		E20102
Remarks		
Pack quantity		1 pcs.