

OGT-HPKG/US100



Range	[mm]	2...600; (white paper 200 x 200 mm 90% remission)
Setting range	[mm]	150...600
Range adjustable		yes
Max. light spot diameter	[mm]	50
Light spot dimensions refer to		at maximum range

OGT200



Diffuse reflection sensor

OGT-HPKG/US100

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 65

Tests / approvals

EMC		EN 60947-5-2
MTTF	[years]	428

Mechanical data

Weight	[g]	53.6
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 72
Thread designation		M18 x 1
Materials		housing: stainless steel (316L/1.4404); operator interface: TPE
Lens material		PMMA

Displays / operating elements

Display	switching status	1 x LED, yellow
Operating elements		potentiometer

Accessories


Items supplied		lock nuts: 2
----------------	--	--------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Connector: 1 x M12; coding: A



Connection

