




Diffuse reflection sensor

OGT-FPKG/2M



- 1 programming buttons
- 2 LED 4 x 90°



Product characteristics

Type of light	red light
Housing	threaded type

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	25
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	624

Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (programmable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	150; (200 (...60 °C))
Switching frequency DC	[Hz]	2000
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range	[mm]	2...800; (white paper 200 x 200 mm 90% remission)
Factory setting		light-on mode
Setting range	[mm]	150...800
Range adjustable		yes



Diffuse reflection sensor

OGT-FPKG/2M

Max. light spot diameter	[mm]	66
Light spot dimensions refer to		at maximum range

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC		EN 60947-5-2
MTTF	[years]	473

Mechanical data

Weight	[g]	136.3
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 80.4
Thread designation		M18 x 1
Materials		stainless steel (316L/1.4404); PA; LCP; EPDM; TPU
Lens material		PMMA

Displays / operating elements

Display	switching status	1 x LED, yellow
Teach function		yes
Electronic lock		yes

Accessories

Items supplied		lock nuts: 2
----------------	--	--------------


Remarks

Remarks		operating voltage "supply class 2" according to cULus
Pack quantity		1 pcs.

Electrical connection

Cable: 2 m, PUR; 3 x 0.34 mm²

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue



Diffuse reflection sensor

OGT-FPKG/2M

Diagrams and graphs

excess gain graph

