



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	C210024	2021/01/12	Vicky	 X1
D	C210235	2021/03/24	Ruru	 X2
E	C222001	2022/12/29	Ruru	 X2





 MI2BXXFL-12BFR-SDXXX

XX: No. Of Pin

XXX: 0.5~99Meters
A05: 0.5 Meter
001: 1 Meter
002: 2 Meters
:
099: 99 Meters

D	Pin Out	5 Gary 灰 4 Black 黑 3 Blue 藍 2 White 白 1 Brown 棕
	Pin # Wire	
C	C2	 5P
	C1	 5P



Note:   
* RoHS Compliant
*  Important dimension
* C1
 Waterproof rate: IP68, mated 1m/24h
IP69K, mated
Housing: Thermoplastic, Black
Pin: Copper alloy, Gold plated
O-Ring: Rubber, Green
Nut: Metal
Outer mold: Thermoplastic, Black
* C2
 Waterproof rate: IP68, mated 1m/24h
IP69K, mated
Housing: Thermoplastic, Black
Pin: Copper alloy, Gold plated
O-Ring: Rubber, Green
Nut: Metal
Outer mold: Thermoplastic, Black
* Cable: UL2517, 22#*5C, OD=5.1mm, PVC Jacket, Black
* Cable length tolerance: 0.5M < L ≤ 1M: +60/-0 mm
1M < L ≤ 3M: +120/-0 mm
3M < L ≤ 5M: +160/-0 mm
5M < L ≤ 10M: ±100 mm
10M < L ≤ 20M: ±200 mm
20M < L ≤ 30M: ±300 mm
30M < L ≤ 99M: ±500 mm

Pin Assignments Front View

UNIT:mm		TITLE	ACC, SEN, B Code, DB-ENDED FF
TOLERANCE	±0.5 mm	SCALE	1:2
		SIZE	A4
		SHEET	1 OF 1
		REV.	E
		WC-REV.	
			Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Vicky	2018-12-11
 MI2BXXFL-12BFR-SDXXX	CHECKED BY	DATE
CUSTOMER	Rita	2018-12-11
ALTW	APPROVED BY	DATE
	Max	2018-12-11