




RoHS Compliant

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	2024.05.13	The first release	Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Technical Specification:

- 1. Current: 80A.
- 2. Torque: 13 lbf.in.
- 3. Mark"▲" is the Critical dimension.



(b)	Spacer	Steel , Matte Tin Plated	1PCS
(a)	terminal	Copper alloy, Matte Tin Plated	1PCS
ITEM	PART NAME	DESCRIPTION	Q`ty

Amphenol ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES I N ANY FORM WHATEVER IS NOT PERMITTED WITHOUTWRITTEN AUTHORITY FROM THE PROPRIETOR.PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE		AMT44008DB Conductive Bracket					
PART NO.		AMT0440008DB0000G		DWG NO.		8AMT0013	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance >30 ±0.60 6-30 ±0.40 0-6 ±0.30 ANGLES ±1°
			Guoxue 2024.05.13	Guoxue 2024.05.13	 SHEET: 01/01		UNIT: mm SCALE: NONE REV.: B