



RoHS Compliant

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	2024.05.15	The first release	Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Technical Specification:

- Current: 50A.
- Torque: 13 lbf.in.
- Mark "▲" is the Critical dimension.



PCB LAYOUT

②	Spacer	Steel , Matte Tin Plated	1PCS
①	terminal	Copper alloy, Matte Tin Plated	1PCS
ITEM	PART NAME	DESCRIPTION	Q`ty

Amphenol ANYTEK	CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUTWRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD		
TITLE	AMT44080DB Conductive Bracket		
PART NO.	AMT0440080DB0000G	DWG NO.	8AMT0020
APPROVED	CHECKED	DESIGNED	DRAWN
		Guoxue 2024.05.15	Guoxue 2024.05.15
		CUST NO.	
		SHEET: 01/01	
		UNIT: mm	
		SCALE: NONE	
		REV.: B	
		Tolerance	
		>30 ±0.60	
		6-30 ±0.40	
		0-6 ±0.30	
		ANGLES ±1°	