



RoHS Compliant



Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	2024.05.15	The first release	Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!!				

Technical Specification:

- Current: 100A.
- Torque: 15 lbf.in.
- Mark"▲" is the Critical dimension.



SECTION A-A



PCB Layout

⑥	Spacer	Steel , Matte Tin Plated	1PCS
①	terminal	Copper alloy, Matte Tin Plated	1PCS
ITEM	PART NAME	DESCRIPTION	Q`ty

Amphenol ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUTWRITTEN AUTHORITY FROM THE PROPRIETOR.PROPERTY OF ANYTEK TECHNOLOGY CO., LTD						
TITLE		AMT45017DB Conductive Bracket								
PART NO.		AMT0450017DB0000G		DWG NO.		8AMT0024				
APPROVED		CHECKED	DESIGNED	DRAWN		CUST NO.		Tolerance		
			Guoxue 2024.05.15	Guoxue 2024.05.15				UNIT: mm		>30 ±0.60
						SCALE: NONE		6-30 ±0.40		
						SHEET: 01/01		0-6 ±0.30		
						REV: B		ANGLES ±1°		