



QOLTEC MINI DISPLAYPORT V1.1 MALE | HDMI A FEMALE | 4K | 0.2M

PRICE: -,-- EUR

SHIPPING TIME: 24 HOURS

CATALOG NUMBER: 50432

EAN CODE: 5901878504322

PRODUCENT: QOLTEC

TYP: MINI DISPLAYPORT MĘSKI / HDMI A ŻEŃSKI

STANDARD: HDMI

PRZEPUSTOWOŚĆ: 10.8 GB/S

ROZDZIELCZOŚĆ: MAX. 4K

CZĘSTOTLIWOŚĆ ODŚWIEŻANIA: MAX. 144 HZ

PRZESTRZEŃ KOLORÓW: ITU-R BT.601, ITU-R BT.709

PRZEZNACZENIE: LAPTOP, PC

FORMAT KOLORÓW: RGB, Y'CBCR 4:4:4, Y'CBCR 4:2:2

GŁĘBIA KOLORÓW: 48 BIT/PX

TRYB TRANSMISJI: RBR, HBR

MAKSYMALNA ILOŚĆ KANAŁÓW AUDIO: 8

TEMPERATURA PRACY: 0°C ~ +70°C

INFORMACJE DODATKOWE: EKRANOWANY

DŁUGOŚĆ KABLA: 0.2 M

KOLOR: CZARNY

OPAKOWANIE: POLYBAG

GŁĘBOKOŚĆ / DŁUGOŚĆ OPAKOWANIA [MM]: 170

WYSOKOŚĆ OPAKOWANIA [MM]: 260

SZEROKOŚĆ OPAKOWANIA [MM]: 15

WAGA NETTO [KG]: 0.0170

WAGA BRUTTO [KG]: 0.0270

GWARANCJA: 24 MIESIĄCE

ITEM DESCRIPTION

ONE CABLE - MANY POSSIBILITIES

IMPORTANT PRESENTATION, A MOVIE FROM GRANDMOTHER'S BIRTHDAY, A SLIDESHOW OF HOLIDAY PHOTOS - YOU CAPTURED ALL THESE MOMENTS AND SAVE TO DISK. YOU SURELY WANT TO SHARE THEM ON A BIG SCREEN WITH FAMILY OR FRIENDS. OUR CABLE IS A PERFECT SOLUTION FOR YOU.

HIGH QUALITY SOLUTIONS

- MAXIMUM RESOLUTION 4K (30HZ), - 8 AUDIO CHANNELS - DIGITAL SURROUND SOUND WILL TRANSFER YOU TO ANOTHER DIMENSION, - 144HZ (1080P) REFRESH RATE WHICH MAKES MOVIES LOOK LIKE ULTRA-SMOOTH, -

DISPLAYPORT CONTENT PROTECTION (DPCP).

IMPORTANCE OF DETAILS

AT THE DESIGN STAGE, ONE OF THE MOST IMPORTANT QUESTION FOR US IS: WHAT ARE CUSTOMER EXPECTATIONS? ACCORDING TO THIS WE PAY ATTENTION TO DETAILS AND USE HIGH QUALITY MATERIALS: - SHIELDING REDUCES THE VOLUME AND INTENSITY OF THE ELECTRICAL NOISE, - NICKEL-PLATED CONNECTOR PROVIDES GREAT SIGNAL PERFORMANCE.

CONFIDENCE CONFIRMED BY A WARRANTY

YOU VALUE THE QUALITY OF PURCHASED EQUIPMENT SO OUR PROJECTS AND SOLUTIONS ARE FOCUSED ON MEETING YOUR EXPECTATIONS. EACH DISPLAYPORT IS COVERED BY 24 MONTHS WARRANTY.