





4.6±0.05
SECTION A-A



P.C.B LAYOUT

MATERIAL:

Insulator : Hi-temp PPS,UL 94V-0,Color:Brown
Contact material : phosphor bronze
Contact plated : Tin plated over nickel

SPECIFICATIONS:

Temperature range : -50°C to 105°C
Current Rating : 1 AMP
Capacitance : 1.0 Picoforads (Max)
Contact Resistance : 30 Milliohms (Max)
Insulation Resistance : 1000 Megohmx (Max)
Withstanding Voltage: AC 600 Vrms
Package : TUBE = Tube

**RoHS
Compliant**

Ninigi

APPD.
核准
DWG.
製圖
DATE 制表日
2023/08/10

SCALE
比例
UNIT
單位
PAGE
張數
1 / 1

TOLERANCE
LINEAR
X ±
X ± 0.38
XX ± 0.25
XXX±
SIZE
紙張尺寸
A 4
REV.
版次
A

PART NAME 品名
PLCC SOCKET SMT TYPE 1.27mm XXP
W/O POLARIZATION PEG
TUBE PACKING TIN PLATING
BROWN COLOR ROHS

PART NO.
料號
PLCC-XXSMD