

DATASHEET

CABLE TIES
LUMINESCENT



INSTALLATION TEMPERATURE	-10°C ÷ 60°C
MOISTURE ABSORPTION	2,7% (23°C - 50% R.H.)
FIRE RESISTANCE OF MATERIAL	UL 94-V2 Halogen-free
RESISTANCE TO	aromatic solvents, oils, greases and their derivatives
LIMITED RESISTANCE	acids
NON-RESISTANT	phenols and chlorinated solvents
WORKING TEMPERATURE	-40°C ÷ 85°C
MATERIAL	polyamide 6.6 natural + luminescent additive

ITEM NO.	SIZE	COLOR	MAX Ø mm	TENSILE STRENGTH (N)
TT3XI00L	2,5x100	natural	22	80
TT3XI50L	2,5x150	natural	35	80
TT3X200L	2,5x200	natural	50	80
TT3X250L	2,5x250	natural	65	80
TT4XI50L	3,6x150	natural	35	178
TT4X200L	3,6x200	natural	50	178
TT4X250L	3,6x250	natural	65	178
TT4X300L	3,6x300	natural	80	178
TT4X370L	3,6x370	natural	100	178
TT5X200L	4,6x200	natural	50	216
TT5X250L	4,6x250	natural	65	216
TT5X300L	4,6x300	natural	80	216
TT5X350L	4,6x350	natural	90	216
TT5X400L	4,6x400	natural	105	216
TT5X450L	4,6x450	natural	120	216
TT5X500L	4,6x500	natural	150	216
TT8X300L	7,6x300	natural	80	540
TT8X400L	7,6x400	natural	105	540
TT8X500L	7,6x500	natural	150	540