

61805600	DATA SHEET	
Valid from: 03.07.2018	SILVYN® LCC-E	

SILVYN® LCC-E is a screw in sleeve for conduit ends with a collar to protect the conduit.

Material: Nickel plated brass

Features: High tensile strength
Robust
Oil resistant
Corrosion resistant
High chemical resistant



Temperature range: -50°C up to +135 °C

Dimension table:

Part No.	Part Name	Nominal size	Length mm	Head height mm	Outer Ø mm	Inner Ø mm
6180 5600	SILVYN® LCC-E	10	16,3	3,6	13,8	5,6
6180 5610	SILVYN® LCC-E	12	16,3	3,6	16,1	8,6
6180 5620	SILVYN® LCC-E	16	21,3	4,3	20	11,5
6180 5630	SILVYN® LCC-E	20	23	4,5	22,9	15,3
6180 5640	SILVYN® LCC-E	25	27,5	6,1	28,7	19,1
6180 5650	SILVYN® LCC-E	32	30	6,6	35	26
6180 5660	SILVYN® LCC-E	40	28	9	47,5	34,6
6180 5670	SILVYN® LCC-E	50	30	10,4	57,9	44,7
6180 5680	SILVYN® LCC-E	63	45	18	69,3	54
6180 5690	SILVYN® LCC-E	75	45	18	83,2	66,4

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: M. Wegerer /PDP Released: DAMU1/PDP	Document: DB61805600EN Version: 01	Page 1 of 1
---	---------------------------------------	-------------