

Transfer or duplication of this document as well as the utilization or communication of its contents are prohibited unless explicit authorization is granted. Violations will be liable for compensation. All rights reserved for patent, utility model or design registrations. 除专利、实用新型、外观设计、发明专利权外，其他权利均归本公司所有。未经许可，不得复制或传播本文件内容。本公司保留所有权利。侵权必究。

FOR-1755 Rev.1.7

2






3

4


5

6

PCB LAYOUT



未注公差/General tolerances (mm)														0.1/10
0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	>500	
3	6	10	18	30	50	80	120	180	250	315	400	500		±2°
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	



4	Pin	Copper	Sn Plated
3	Nut	Copper alloy	/
2	Dust Mat	EVA	/
1	Housing	PBT	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

UL 标准/UL Standard:		B	C	D
额定电压/电流/Rated Voltage(V)/Current(A)		300/15	/	300/10
IEC 标准/IEC Standard:				
过压类别/Overvoltage Category/污染等级/Pollution Degree		III/3	III/2	II/2
额定电压/电流/Rated Voltage(V)/Current(A)		/	320/20	/
额定脉冲电压(KV)/Rate Impulse Voltage(KV)		/	4	/
间距/Pitch(mm)/线数范围/Poles		5.08/N=02~22P		
使用温度范围/Operating temperature(°C)		-30~+120		
符合RoHS环保要求/Conform to RoHS		Yes		
标准颜色编号/Standard color number: PANTONE / RAL		/		



APPD:	兰春华	2023.02.13
CHKD:	龚耀志	2023.02.13

DRFT:	刘强	2023.02.10
-------	----	------------

MATERIAL:		SURFACE/COLOR:		
MAT NO./REV:		/ 00	MAT STATUS: 批量	
NAME				
2CDGRM-5.08-XXP-1Y-00Z (H)				
DRAWING NO.	TYPE	DRAWING STATUS	SCALE	SHEET
200030938	CUSTOMER DRAWING	已发布	2:1	1/1

00	REV	ECN	DESCRIPTION	DRFT	DATE
00				刘强	2023.02.10

1

2

3

4

5

6