



HELUTOP® Easy

Threadless cable gland for easy and quick installation with patented spring/snap system without tools.

Advantages:

- No tools required for installation
- No threaded holes required
- No locknuts required
- Same clamping range as HELUTOP® HT-Series
- VDE-according to DIN EN 62444
- Gland and cable will be fixed with clockwise thread
- Installation in tight areas and no-access spaces (locknut side)
- Cable gland fits as tightly as traditional gland held in place with threaded hole or locknut
- Hexagon of body and cap are same SW
- Large wall thickness range: 0,5 – 4,0 mm
- Quick and easy disassembly with separate tool. No damage to cable gland or wall

Material

PA 6, V2 acc. to UL 94
Seal: Chloroprene-rubber (CR)

Note

Additional colors on request: red RAL 3020, white RAL 9003, blau RAL 5015.
Dimensions borehole Ø = +/- 0.1

Technical data

Protection class: IP66 / IP68 - 5 bar

Temperature range: -20°C up to +100°C
Temperature range temporary: -30°C up to +150°C

Part no. light grey RAL 7035	Part no. dark grey RAL 7001	Part no. black RAL 9005	ØDrill hole / Metr.	Cable Ø from / to mm	Spanner size mm	Unit	Net EUR/100 items at a purchase of		
							up to 100	101 - 500	501 - 1000
908054	908060	908062	16,3 / M16	5,0 - 10,0	22	50	o. r.	o. r.	o. r.
908055	908061	908063	20,3 / M20	6,0 - 12,0	24	50	o. r.	o. r.	o. r.
908368	908383	908385	25,3 / M25	11,0 - 17,0	29	25	o. r.	o. r.	o. r.
908369	908384	908386	32,3 / M32	15,0 - 21,0	36	25	o. r.	o. r.	o. r.

Disassembly tool

Part no.	Type	Unit	Net EUR/item at a purchase of		
			1	2 - 4	5 - 10
908056	Disassembly tool for Ø16 and Ø20	1	o. r.	o. r.	o. r.
908387	Disassembly tool for Ø25 and Ø32	1	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request