

DIGITUS Wireless HDMI Receiver for DS-55346

DS-55347

EAN 4016032496625



Wireless HDMI Receiver for DS-55346, Full HD

The additional receiver unit for the Wireless HDMI Extender Set / Splitter Set (DS-55346) extends this Multicast system by up to 4 receiver modules and receives your high-resolution HDMI video and audio signals without a cable at a distance of up to 100 m (1:1 connection, unrestricted view). Distribute your media content quickly and easily on up to 4 displays.

Extend the Wireless HDMI Extender / Splitter Set (DS-55346) with additional receiver units and distribute AV signals on up to 4 output displays

- Extends DS-55346 with additional receiver units
- Distribute your HDMI signal on up to 4 displays (receivers)
- Transfer of HDMI signals in Full HD with max. resolution of 1080p / 60 Hz
- IR transmission to control the source device from output display
- Plug & Play - no software or driver required
- HDMI 1.4, HDCP 1.3
- Transmission distance 1:1 connection: up to 100 m (unobstructed view)
- Transmission distance 1:2 connection: up to 60 m (unobstructed view)
- Transmission distance 1:3 connection: up to 45 m (unobstructed view)
- Transmission distance 1:4 connection: up to 25 m (unobstructed view)
- Frequency: 5 GHz
- Wireless standard: 802.11a
- HDMI transfer rate: 6.75 Gbps
- Compression: H.264

- Transfer latency: 150 - 200 ms
- Receiver connections:
 - 1 x HDMI (output) - Connection output display
 - 1 x IR (input) - Connection IR cable
 - 1x Power adapter (DC/5V)
 - 1x Reset button
- LED displays: Power / Link / Status
- Operating temperature: 0°C - 50°C
- Power consumption: approx. 1.5 W
- Dimensions: L 11.8 x W 6.35 x H 1.8 cm
- Color: black
- Weight receiver: 170 g
- Housing material: Metal
- Note: The transmission distance with a restricted visual range cannot be determined generally and depends on the specific circumstances where installed
- Note: Walls, glass etc. shorten the signal range or cause signal losses
- HDTV Resolution max.: 1920 x 1080 Pixel, 60Hz
- HDTV Standard: 1080p
- KVM: no
- PoE (Power over Ethernet): no
- Video connection ports: HDMI

Package contents

- 1x Receiver unit
- 1x Antenna
- 1x Power adapter, cable length: 1.2 m
- 1 x IR connection cable, 1.2 m
- 1x User manual

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm ³
Packaging Unit Carton	20	8.70	48.20	41.50	20.70	41,406.20
Packaging Unit Inside	1	0.44	0.00	0.00	0.00	0.00
Packaging Unit Single	1	0.44	19.70	18.60	4.50	1,648.89
Net single without Packaging	1	0.31	19.70	18.60	4.50	1,648.89

The image is a 3x3 grid of promotional material for the DIGITUS DS-55347 Wireless HDMI Receiver. The top row contains three photographs of the device: a side profile, a front view with the antenna, and a back view showing ports. The middle row contains three versions of the product's feature list and connectivity diagram. The bottom row contains three lifestyle images: the device on a desk, the device on a shelf with other electronics, and the device in a gaming setup with a monitor and laptop.

Product Features (repeated in all middle-row images):

- 1080p @ 60Hz: High Resolution
- 3.5Gbps: Transmission Distance
- 0.1s Delay: Plug and Play
- 4Kx2K: Multi-Use
- 100m: Range
- 2.4GHz: Frequency
- 100m: Range
- 0.1s: Delay
- 4Kx2K: Multi-Use

Connectivity Diagrams (repeated in all middle-row images):

- DS-55347 (Tx) - Transmitter:** Connected to PC, Laptop, PS4, Xbox, and other devices.
- DS-55347 (Rx) - Receiver:** Connected to TV, Monitor, and other displays.
- DS-55347 (Tx) - Transmitter:** Connected to PC, Laptop, PS4, Xbox, and other devices.
- DS-55347 (Rx) - Receiver:** Connected to TV, Monitor, and other displays.

Lifestyle Images (bottom row):

- DS-55347 Wireless HDMI Receiver for DS-55346: Device on a desk.
- DS-55347 Wireless HDMI Receiver for DS-55346: Device on a shelf with other electronics.
- DS-55347 Wireless HDMI Receiver for DS-55346: Device in a gaming setup with a monitor and laptop.

- Please read these instructions carefully before using the appliance and keep them for future reference.
- For indoor use only.
- Do not use the device in a damp environment or near water.
- Do not expose the product to extremely high or low temperatures, strong light sources or direct sunlight.
- This product is not a toy. Keep it out of the reach of children.
- Do not connect the adapter to the mains until you have made sure that the mains voltage corresponds to the value specified on the rating plate.
- Never connect the power supply unit if it is damaged. In such cases, please contact your supplier.
- Disconnect the AC/DC mains adapter from the power supply if the appliance is not to be used for a longer period of time.
- Never open the product: The appliance may contain parts with lethal voltage. Repairs or maintenance should only be carried out by qualified personnel.
- Improper use, modifications or repairs carried out by the user will invalidate all warranties.
- - We accept no product responsibility for improper or non-intended use of the product.

ASSMANN Electronic GmbH
Auf dem Schüffel 3
Lüdenscheid, Germany
<https://www.assmann.com>
info@assmann.com