



- 1.CABLE:UL2725,28AWG(7/0.12mm)×1PAIRS
+24AWG(7/0.2mm)×2C,TIN COPPER
INSULATOR:P.P FOR 28AWG&PVC 24AWG
SHIELD:AL-FOIL+DRAIN WIRE+BRAID
JACKET:PVC,COLOR:GREY,Ø.D:4.8mm±0.2mm
- 2.CONNECTOR:1 PCS USB A SOLDER TYPE MALE
SHELL:GOLD PLATED
- 3.CONNECTOR:1 PCS USB B SOLDER TYPE MALE
SHELL:GOLD PLATED
- 4.HOOD:MOULDED GREY COLOR
- 5.Fulfill ROHS Guideline
- 6.ELECTRONIC TEST:100% OPEN SHORT+MISS WIRE TEST

WIRE LIST

P1		P2	
USB A MALE(GOLD)	WIRE COLOR	USB B MALE(GOLD)	AWG
1	RED	1	24AWG
2	WHITE	2	1 PAIRS (28AWG)
3	GREEN	3	
4	BLACK	4	24AWG
SHELL	DRAIN	SHELL	

PART NO	CAB-USBAB3G GY	SHEET NO	1	THIRD ANGLE PROJECTION	有得 限望 公股 司份 NEWMAN, HOPE & CO.INC TEL:886-2-28765517,FAX:886-2-28765527 E-MAIL: sales@newmanhope.com.tw
TITLE:USB A MALE TO USB B MALE L:3.0M,GOLD PLATED UL2725 CABLE GREY COLOR				SCALE N.T.S SIZE A4 UNIT ☒ mm ☐ INCH	DRAWN BY & DATE CHECKED BY & DATE APPROVED BY & DATE
DWN NO	D-CAB-USBAB-3G GY				