


BNC Jack, right angle, PCB mount, 50 Ohm



6	WASHER	1	STEEL	NICKEL	UNLESS OTHERWISE SPECIFIED 1. REMOVE ALL BURRS. 2. BREAK ALL CONNERS & EDGES CO. 15 MAX. 3. CHAMFER 1ST & LAST THREADS 45°. 4. DIAMETERS ON COMMON CENTERS. TO BE CONCENTRIC WITHIN 0.01 T. I. R. 5. ALL DIMENSIONS ARE AFTER PLATING.	MAJOR DIMENSIONS		
5	NUT	1	BRASS	NICKEL		UNLESS OTHERWISE NOTED TOLERANCES 0.5-6=±0.2 6-30=±0.4 30-120=±0.6 ANGLES=±5°		
4	PIN	1	BRASS	GOLD				
3	INSULATOR	1	DELRIN	WHITE				
2	BODY 2	1	TP	WHITE				
1	BODY 1	1	ZINC	NICKEL				
NO	Description	Q' ty	Material	Finish			UNIT	MM