






SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
OPEN	1-2



- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X = ± 0.4
 X.XX = ± 0.25
 3. TERMINAL NUMBERS FOR REF ONLY
 4. CONTACT MATERIAL: SILVER
 5. RATING: 20A/250VAC
 6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
 AT FULL LOAD.
 7. INSULATION RESISTANCE: 100M Ω @ 500VDC
 8. DIELECTRIC STRENGTH: 1,500 VAC
 9. CONTACT RESISTANCE: 50m Ω
 10. OPERATING TEMP.: -40°C to 85°C
 11. TRAVEL: 3.5mm
 12. ▲ DENOTES CRITICAL PARAMETER.
 - ▲ 13. LAMP VOLTAGE: 12V
 - ▲ 14. ILLUMINATION COLOR: RED
 - ▲ 15. INGRESS PROTECTION: IP67
 - ▲ 16. HARDWARE SUPPLIED: O-RING AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY					OBJECT ID
A	ECO-102939	Release	09/13/24	MW	TITLE PVHC7F23SS314				100128245
					SCALE 3:2	DATE 8/14/2024	DR MW	DWG 52-PVHC7F23SS314	REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
 E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED