

LogiLink®

USB-C 3.2 to RJ45 Ethernet Cable

Art. No.: CU0410

CU0411

CU0412

CU0413

CU0414

CU0415

CU0416

CU0417

With LogiLink USB-C to Ethernet cable, you can connect router, modem or network switch to USB-C port of laptop or tablet directly. Ethernet is immediately available without any extra drivers.

Features:

- » Connect router, modem or network switch to USB-C port of laptop, tablet or smartphone
- » USB-C 3.2 Gen 1 male to RJ45 male 8P8C
- » Cat.6 interference-free S/FTP cable
- » Cable material: Flexible textile
- » Transmission rate up to 1 Gbps
- » Plug and play
- » Cable length available from 1–15 m

*The ethernet cable is not suitable as a rollover cable for game consoles.



Premium braided cable ensures max. durability and flexibility



USB-C connection (compatible with Thunderbolt 3/4)

Cat.6

Gigabit Ethernet
10/100/1000

Textile
Cable

Plug
&
Play



Available cable length from 1–15 m



*The specifications and pictures are subject to change without prior notice.

*All trade names referenced are the registered trademarks of their respective owners.

Specifications:

Connection 1	RJ45 male (8P8C)
Connection 2	USB-C male
USB Version	3.2 Gen 1
Transmission Rate	Up to 1 Gbps
Cable Sheath	Ø4.8±0.2 mm
Color	Black

Art-No.	Cable Length	EAN Code
CU0410	1 m	4052792075229
CU0411	1.5 m	4052792075236
CU0412	2 m	4052792075243
CU0413	3 m	4052792075250
CU0414	5 m	4052792075267
CU0415	7.5 m	4052792075274
CU0416	10 m	4052792075281
CU0417	15 m	4052792075298

Package Content:

» 1 x USB-C to Ethernet Cable

Package Information:

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
CU0410	180 x 200 mm	0.042 kg	390 x 330 x 280 mm	200 pcs	9.4 kg
CU0411	180 x 200 mm	0.048 kg	390 x 330 x 280 mm	150 pcs	8.2 kg
CU0412	180 x 230 mm	0.063 kg	390 x 330 x 280 mm	120 pcs	8.5 kg
CU0413	180 x 230 mm	0.084 kg	390 x 330 x 280 mm	100 pcs	9.4 kg
CU0414	240 x 240 mm	0.133 kg	390 x 330 x 280 mm	80 pcs	11.6 kg
CU0415	240 x 240 mm	0.188 kg	390 x 330 x 280 mm	40 pcs	8.5 kg
CU0416	280 x 280 mm	0.243 kg	390 x 330 x 280 mm	30 pcs	8.3 kg
CU0417	280 x 280 mm	0.450 kg	390 x 330 x 280 mm	20 pcs	10 kg