

Cotton braided Micro-USB cable with metal connectors, 1.8 m, black

CCDB-mUSB2B-AMBM-6

- Perfect for connecting or charging smartphones, tablets, etc
- Gold plated connectors for a reliable connection
- Stylish design with cotton braiding and premium quality metal connectors



Specifications

Interface: USB 2.0
 Connector 1: USB Type-A (male)
 Connector 2: USB micro-B (male)
 Data transfer rate: 480 Mbps
 Charging power: 2.1 A
 DisplayPort Alt Mode: not supported
 Jacket braiding: Cotton
 Connector style: metal
 Cable length: 1.8 m (6 ft)

Features

- Male A plug to male Micro-B plug USB 2.0 charging and data cable
- Gold-plated contacts for reliable high-speed data transfer
- Cotton braided jacket

Packaging

Q'ty in crtn, pcs	40
Crtn volume, CUM	0.008
Crtn weight, kgs	2.03
Individual package size LxWxH:	20x155x40 mm
Carton size LxWxH:	200x180x235 mm
Country of origin	CN
Barcode	8716309128230
Customs code	8544429090

Certificates

