

AW	00 0 0 X 0					X	X	X	X	X
	Color									
	F Semitransparent					0000 Standard		G ROHS compliant (lead<4%) In copper alloy		
DS-240	XX		X	X		X	X	X	X	
	Number of contacts		Body type	Color						
	End Stackable 01 1 contacts 02 2 contacts 03 3 contacts 24 24 contacts		0 Standard 1 With snap-in mounting feet	0 Black 5 Green(RAL 6018/T) 6 Blue(RAL 5015/A) 8 Grey(RAL 7004/P)		000 Standard Any special item by customer request, please contact sales department.		G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy		
E2	XX		X	X	X	X	X	X	X	X
	Number of contacts		Pitch	Screw&Clamp	Color	Body type				
	Solid Block 02 2 contacts 03 3 contacts 24 24 contacts		1 3.5/.138"	0 "+/-" Combination type screw W/Brass Machined Clamp 1 "-." Slotted screw W/Brass Machined Clamp	0 Black 3 Orange 5 Green(RAL 6018/T) 6 Blue(RAL 5015/A) 8 Grey(RAL 7035/D) C Green(RAL 6018/U)	0 W/O flange	0000 Standard (Steel screw plating Cr ³⁺) Any special item by customer request, please contact sales department.		G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy	
E4	XX		0	X	X	0	X	X	X	X
	Number of contacts			Screw&Clamp	Color					
	Solid Block 02 2 contacts 03 3 contacts 04 4 contacts 06 6 contacts			0 "+/-" Combination type screw W/Brass Machined Clamp 1 "-." Slotted screw W/Brass Machined Clamp	0 Black 5 Green(RAL 6018/T) 6 Blue 8 Grey(RAL 7035/D) C Green(RAL 6018/U)		0000 Standard (Steel screw plating Cr ³⁺) Any special item by customer request, please contact sales department.		G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy	
E5	XX		X	X	X	0	X	X	X	X
	Number of contacts		Pitch	Screw&Clamp	Color					
	Solid Block 06 2*3 contacts 08 2*4 contacts 48 2*24 contacts 28 2*14 contacts 32 2*16 contacts		0 6.35/.25"	Screw type 0 "+/-" Combination type screw W/Brass Machined Clamp 1 "-." Slotted screw W/Brass Machined Clamp B Screwless type	0 Black 2 Red 3 Orange 4 Yellow 5 Green (RAL 6018/T) 6 Blue 8 Grey 9 White C Green (RAL 6018/U)		0000 "@ Logo(Standard) 000A "ANYTEK" Mark Any special item by customer request, please contact sales department.		G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy	