

|           |                                                                                             |             |   |                                                                                                      |   |                                                                                             |   |   |   |                                                                                                   |
|-----------|---------------------------------------------------------------------------------------------|-------------|---|------------------------------------------------------------------------------------------------------|---|---------------------------------------------------------------------------------------------|---|---|---|---------------------------------------------------------------------------------------------------|
| <b>H9</b> | XX<br>Number of contacts                                                                    | X<br>Pitch  | 0 | X<br>Color                                                                                           | 0 | X                                                                                           | X | X | X | X                                                                                                 |
|           | End Stackable<br>01 1 contacts<br>02 2 contacts<br>03 3 contacts<br>.. ..<br>24 24 contacts | 5 5.08/.20" |   | 0 Black<br>3 Orange (RAL 2011/P)<br>5 Green (RAL 6018/T)<br>8 Grey (RAL 7004/P)<br>C Multiple colors |   | 0000 Standard<br><br>Any special item by customer request, please contact sales department. |   |   |   | G ROHS compliant (lead<4%) In copper alloy<br><br>H ROHS compliant (lead<1000ppm) In copper alloy |

|           |                                                                                                                                                                                                |                                                                                                        |                                                               |                                                                                      |   |                                                                                             |   |   |   |                                                                                                   |
|-----------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|---------------------------------------------------------------|--------------------------------------------------------------------------------------|---|---------------------------------------------------------------------------------------------|---|---|---|---------------------------------------------------------------------------------------------------|
| <b>HA</b> | XX<br>Number of contacts                                                                                                                                                                       | X<br>Pitch                                                                                             | X<br>Insulator                                                | X<br>Color                                                                           | 0 | X                                                                                           | X | X | X | X                                                                                                 |
|           | End Stackable<br>01 1 contacts<br>02 2 contacts<br>03 3 contacts<br>.. ..<br>24 24 contacts (pitch 2.54&3.81&5.0&5.08)<br>16 16 contacts (pitch 7.5&7.62)<br>12 12 contacts (pitch 10.0&10.16) | 0 5.08/.20"<br>2 7.62/.30"<br>3 5.0/.197"<br>4 10.0/.394"<br>5 2.54/.10"<br>6 7.5/.295"<br>7 3.81/.15" | 0 Vertical (90D wire inlet)<br>1 Horizontal (180D wire inlet) | 0 Black<br>2 Red<br>5 Green (RAL 6018/T)<br>8 Grey (RAL 7004/P)<br>C Multiple colors |   | 0000 Standard<br><br>Any special item by customer request, please contact sales department. |   |   |   | G ROHS compliant (lead<4%) In copper alloy<br><br>H ROHS compliant (lead<1000ppm) In copper alloy |

|           |                                                                                                                                                                                |                                                                           |                                                    |                                                                              |                                                    |                                                                                             |   |   |   |                                                                                                   |
|-----------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------|----------------------------------------------------|------------------------------------------------------------------------------|----------------------------------------------------|---------------------------------------------------------------------------------------------|---|---|---|---------------------------------------------------------------------------------------------------|
| <b>HB</b> | XX<br>Number of contacts                                                                                                                                                       | X<br>Pitch                                                                | X<br>Body type                                     | X<br>Color                                                                   | X<br>Lever                                         | X                                                                                           | X | X | X | X                                                                                                 |
|           | End Stackable<br>01 1 contacts<br>02 2 contacts<br>03 3 contacts<br>.. ..<br>24 24 contacts (pitch 3.81&3.96&5.0)<br>16 16 contacts (pitch 7.5)<br>12 12 contacts (pitch 10.0) | 0 5.0/.197"<br>1 10.0/.394"<br>2 7.5/.295"<br>3 3.81/.15"<br>4 3.96/.156" | 1 Single wire<br>2 Double wire (only 5.0/7.5/10.0) | 0 Black<br>2 Red (RAL 3001/D)<br>5 Green (RAL 6018/T)<br>8 Grey (RAL 7004/P) | 0 With lever<br>1 Without lever (Only single wire) | 0000 Standard<br><br>Any special item by customer request, please contact sales department. |   |   |   | G ROHS compliant (lead<4%) In copper alloy<br><br>H ROHS compliant (lead<1000ppm) In copper alloy |

|           |                                                                                                                                           |                                           |                                               |                                                                                                                 |                                                                                                                                                                |                                                                                             |   |   |   |                                                                                                   |
|-----------|-------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|---|---|---|---------------------------------------------------------------------------------------------------|
| <b>HC</b> | XX<br>Number of contacts                                                                                                                  | X<br>Pitch                                | X<br>Lever                                    | X<br>Color                                                                                                      | X<br>Foot print                                                                                                                                                | X                                                                                           | X | X | X | X                                                                                                 |
|           | End Stackable<br>01 1 contacts<br>02 2 contacts<br>03 3 contacts<br>.. ..<br>24 24 contacts (pitch 2.5&3.5)<br>12 12 contacts (pitch 7.0) | 0 3.5/.138"<br>1 7.0/.276"<br>B 2.5/.098" | 0 Standard<br>2 High profile (only pitch 2.5) | 2 Red (RAL 3001/D)<br>3 Orange (RAL 2011/P)<br>5 Green (RAL 6018/T)<br>8 Grey (RAL 7004/P)<br>C Multiple colors | 0 Double row center contact link together with end cover<br>1 Side single row<br>2 Center single row<br>3 Double row side contact link together with end cover | 0000 Standard<br><br>Any special item by customer request, please contact sales department. |   |   |   | G ROHS compliant (lead<4%) In copper alloy<br><br>H ROHS compliant (lead<1000ppm) In copper alloy |

|           |                                                                          |             |   |                                                     |                 |                                                                                             |   |   |   |                                                                                                   |
|-----------|--------------------------------------------------------------------------|-------------|---|-----------------------------------------------------|-----------------|---------------------------------------------------------------------------------------------|---|---|---|---------------------------------------------------------------------------------------------------|
| <b>HD</b> | XX<br>Number of contacts                                                 | X<br>Pitch  | 0 | X<br>Color                                          | X<br>Foot print | X                                                                                           | X | X | X | X                                                                                                 |
|           | Solid Block<br>02 2 contacts<br>03 3 contacts<br>.. ..<br>24 24 contacts | 0 5.08/.20" |   | 8 Grey body(RAL 7004/P)<br>Orange lever(RAL 2011/P) | 0 Double row    | 0000 Standard<br><br>Any special item by customer request, please contact sales department. |   |   |   | G ROHS compliant (lead<4%) In copper alloy<br><br>H ROHS compliant (lead<1000ppm) In copper alloy |