

NU	XX Number of contacts	X Pitch	0	X Color	0	X	X	X	X	X
	End Stackable 01 1 contacts 02 2 contacts 24 24 contacts	0 3.5/.138"	0 Black(RAL 9005) 2 Red(RAL 3001/D) 3 Orange(RAL 2011/P) 4 Yellow(RAL 1018/A) 5 Green(RAL 6018/T) 6 Blue(RAL 5015/A) 8 Grey(RAL 7004/P) 9 White(RAL 1102) C Multiple colors	0000 Standard Any special item by customer request, please contact sales department.	G ROHS compliant (lead<4%) In copper alloy					

NX	XX Number of contacts	X Pitch	0	X Color	0	X	X	X	X	X
	End Stackable 01 1 contacts 02 2 contacts 24 24 contacts	0 5.0/.197"	0 Black(RAL 9005) 2 Red(RAL 3001/D) 3 Orange(RAL 2011/P) 4 Yellow(RAL 1018/A) 5 Green(RAL 6018/T) 6 Blue(RAL 5015/A) 8 Grey(RAL 7004/P) 9 White(RAL 1102) C Multiple colors	0000 Standard Any special item by customer request, please contact sales department.	G ROHS compliant (lead<4%) In copper alloy					

NY	XX Number of contacts	X Pitch	0	X Color	X Cover type	X	X	X	X	X
	End Stackable 02 2 contacts 03 3 contacts 24 24 contacts (pitch 3.5) 12 12 contacts (pitch 7.0)	1 3.5/.138" 2 7.0/.276"	0 Black 2 Red 3 Orange 4 Yellow 5 Green(RAL 6018/T) 6 Blue 8 Grey(RAL 7004/P) 9 White C Multiple colors	0 Without cover 1 With cover	0000 Standard Any special item by customer request, please contact sales department.	G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy				

NZ	XX Number of contacts	X Pitch	0	X Color	X Body type	X	X	X	X	X
	End Stackable 01 1 contacts 02 2 contacts 03 3 contacts 12 12 contacts (pitch 15.0) 08 8 contacts (pitch 15.0)	0 10.0/.393" 1 15.0/.591" 2 7.5/.295"	0 Black 1 Natural color 2 Red 3 Orange 4 Yellow 5 Green 6 Blue 8 Grey 9 White C Multiple colors	A With jumper slot B Without jumper slot C Without jumper slot(Round hole) (Interlace tail type) D Without jumper slot(Round hole) (Parallel tail type) E Without jumper slot(Square hole) (Interlace tail type) F Without jumper slot(Square hole) (Parallel tail type)	0000 Standard Any special item by customer request, please contact sales department.	G ROHS compliant (lead<4%) In copper alloy				

OL	XX Number of contacts	X Pitch	X Pin length	X Pin plating	X Material of body	X	X	X	X	X
	Solid Block 02 2 contacts 03 3 contacts 24 24 contacts (pitch 3.5) 12 12 contacts (pitch 7.0)	1 3.5/.138" 2 7.0/.276"	0 L=16.5mm(Φ1.3)(DIM A=3.5mm)	0 Tin 1 Gold plating 10u" 2 Gold flash	0 DIP type 1 THR type	0000 Standard Any special item by customer request, please contact sales department.	G ROHS compliant (lead<4%) In copper alloy			