

T2

XX Number of contacts	X Pitch	X Screw&Clamp	X Color	X Insulator type	☒	☒	☒	☒	☒
End Stackable 02 2 contacts 03 3 contacts 24 24 contacts (pitch 5.0&5.08) 12 12 contacts (pitch 10.0&10.16)	0 5.0/.197" 1 10.0/.394" 2 5.08/0.20" 3 10.16/0.40"	0 "+/-" Combination type W/Brass Machined Clamp 1 "-" Slotted screw W/Brass Machined Clamp	0 Black 5 Green (RAL 6018/T) 6 Blue 8 Grey (RAL 7035/D) C Green (RAL 6018/U)	0 Stackable 1 Solid block	0000 Standard (Steel screw plating Cr ³⁺) Any special item by customer request, please contact sales department.				G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy

T3

XX Number of contacts	X Pitch	X Screw&Clamp	X Color	X Body type	☒	☒	☒	☒	☒
02 2 contacts 03 3 contacts 24 24 contacts (pitch 5.0) 12 12 contacts (pitch 10.0)	0 5.0/.197" 1 10.0/.394"	4 "+/-" Combination type W/Brass Stamping Clamp 5 "-" Slotted screw W/Brass Stamping Clamp	0 Black 2 Red 3 Orange 4 Yellow 5 Green (RAL 6018/T) 6 Blue 8 Grey 9 White C Green (RAL 6018/U)	1 Stackable (180D wire inlet) 3 Stackable (90D wire inlet) 4 Solid block (180D wire inlet) 5 Solid block (90D wire inlet)	0000 Standard (Steel screw plating Cr ³⁺) Any special item by customer request, please contact sales department.				F RoHS compliant (lead<100ppm) In copper Alloy G RoHS compliant (lead<4%) In copper Alloy H RoHS compliant (lead<1000ppm) In copper Alloy

T4

XX Number of contacts	X Pitch	X Screw&Clamp	X Color	X Tail length	☒	☒	☒	☒	☒
Solid Block 02 2 contacts 03 3 contacts 24 24 contacts (pitch 5.0) 12 12 contacts (pitch 10.0) 16 16 contacts (pitch 7.5)	0 5.0/.197" 1 10.0/.394" 2 7.5/.295"	4 "+/-" Combination type W/Brass Stamping Clamp 5 "-" Slotted screw W/Brass Stamping Clamp	0 Black 5 Green (RAL 6018/T) 6 Blue 8 Grey (RAL 7035/D)	0 4.4mm 1 3.0mm 2 4.4mm (Connector through type) 3 3.0mm (Connector through type)	0000 Standard (Steel screw plating Cr ³⁺) Any special item by customer request, please contact sales department.				G ROHS compliant (lead<4%) In copper alloy

T5

XX Number of contacts	X Pitch	X Screw&Clamp	X Color	X Tail length	☒	☒	☒	☒	☒
Solid Block 02 2 contacts 03 3 contacts 24 24 contacts (pitch 3.5) 12 12 contacts (pitch 7.0)	0 3.5/.138" 1 7.0/.276"	0 "+/-" Combination type W/Brass Machined Clamp 1 "-" Slotted screw W/Brass Machined Clamp	0 Black 5 Green (RAL 6018/T) 6 Blue 8 Grey (RAL 7035/D)	0 3.5mm	0000 Standard (Steel screw plating Cr ³⁺) Any special item by customer request, please contact sales department.				G ROHS compliant (lead<4%) In copper alloy

T7

XX Number of contacts	X Pitch	X Screw&Clamp	X Color	X PCB mounting	☒	☒	☒	☒	☒
End Stackable 02 2 contacts 03 3 contacts 16 16 contacts (pitch 6.35&7.62&9.52) 08 8 contacts (pitch 12.7&15.24&19.04)	0 6.35/.25" 1 12.7/.5" 2 9.52/.374" 3 19.04/.748" 4 7.62/0.3" 5 15.24/0.6"	2 "+/-" Combination type W/Brass Machined Clamp 3 "-" Slotted screw W/Brass Machined Clamp	0 Black 5 Green (RAL 6018/T) 6 Blue 8 Grey (RAL 7035/D) C Green (RAL 6018/U)	0 Vertical(180D) 1 45D (only pitch 9.52&6.35)	0000 Standard (Steel screw plating Cr ³⁺) Any special item by customer request, please contact sales department.				G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy