









- RJ45 CONTACTS
- RJ45 SHELL GROUND CONTACT
- CONNECTOR LOCATION PINS



3D VIEW
1:1



PANEL CUT OUT
3:2
(CONNECTOR FRONT VIEW)

TABLE OF PART NUMBERS

PART No.	FINISH	TRANS. CLASS
RJXS8FG3VB	NICKEL PLATE	CLASS D
RJXS8FG5VB	NICKEL PLATE	CAT5e
RJXS8FG6VB	NICKEL PLATE	CAT6



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE				THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER.				Amphenol Amphenol Australia Pty.Ltd, 22 Industry Blvd, Carrum Downs VIC 3201 Australia	
LINEAR		ANGULAR		MATERIAL: REFER SPECIFICATION		DRN: T.N	DATE: 04/03/20	TITLE: XLRnet CONNECTOR VERT IP54 WITH CAP CUSTOMER DRAWING	
X ±0.5		X' ±1				CKD: P.M	DATE: 04/03/20	PART No: SEE TABLE OF P/No. 1	
X.X ±0.1		X.X' ±30'				APP'D: P.M	DATE: 04/03/20	REV SHEET 2/2	
X.X ±0.05		X.X'X' ±15'				SCALE: 3:2	SIZE: A3	DRAWING No. 55011396-000	
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS									
DO NOT SCALE									
DIMENSIONS IN MILLIMETRES				THIRD ANGLE PROJECTION					